



INSTRUCTIONS FOR ASSEMBLING CIRCLINE TUBE IN DAZOR MAGNIFIER


1. Note the position of the clamp finger (B) directed up and out over the tube.
2. Remove thumbscrews (A) and clamp fingers (B).
3. *Position circline fluorescent tube (C) with lamp pins facing the socket. Be sure to have the **FLAT** side of the socket on **TOP** and facing you while installing the bulb.
4. Connect the bulb to the socket.
5. Replace the thumbscrews (A).




*VIEW LOOKING DOWN ON TOP OF SOCKET



FLAT SIDE OF
SOCKET ON TOP



ADD-A-LENS




DAZOR ADD-A-LENS® (optional accessory) ADD-A-LENS #1400

The 8-diopter ADD-A-LENS accessory increases magnification of a 3-diopter lens from +75% to +275% (11-diopter).

INSTRUCTIONS FOR ASSEMBLING

1. Remove thumbscrews (A) but leave clamp fingers (B) in position.
2. Position ADD-A-LENS over clamp fingers (B) and replace thumbscrews (A).



DAZOR®
DAZOR MANUFACTURING CORP.
2079 Congressional
St. Louis, MO 63146

800-345-9103 ~ 314-652-2400 ~ 314-652-2069 Fax
www.dazor.com ~ info@dazor.com

Form 8FM100-12

Circline Illuminated Magnifiers MC-Series

Light and Magnification Combine for Comfortable Viewing of Small Details

Lens:

- 5-inch diameter
- Crown optical glass
- Crystal clear
- Distortion free

Light Source:

- 22-watt Circline fluorescent
- Multiple color temperature bulbs available
- Even, shadow-free light for optimum brightness and accuracy
- Protective bulb shield standard

Interlocking arm channels for extra strength.

Finish:

- Powder coated
- Maximum durability
- Environmentally safe

Floating Arm:


- All-metal channels
- Sleek design
- No exposed springs
- Hygienic
- Easy to move
- Stays in position

Precision, counterbalanced spring for years of failure-free use.

IV-Pivot interchanges with clamp, pedestal or caster floor stand. Weighted desk base models also available.

7100-093 Standard dual-clamp has two heavy duty studs that prevents the base from moving and twisting off horizontal surfaces. Robust, all metal construction, unsurpassed in task lighting market.

Optional: Adjustable clamp-on base can mount on any vertical, horizontal or slanted surface. It can clamp onto the right, left, top or back side of a tilted tabletop (7100-08).



Stylish 8MC-series magnifiers cast an even glow on your task for optimum brightness and accuracy. These magnifiers reduce eyestrain and fatigue by combining the two key factors in aiding our vision — **Light and Magnification.**

Available Lenses:

- 3-diopter (+75% magnification)
- 5-diopter (+125% magnification)
- 11-diopter (+275% magnification)
- 16-diopter (+400% magnification)



MADE IN U.S.A.



DAZOR®

DAZOR MANUFACTURING CORP.

2079 Congressional

St. Louis, MO 63146

800-345-9103 ~ 314-652-2400 ~ 314-652-2069 Fax

www.dazor.com ~ info@dazor.com

MOUNTING OPTIONS FOR DAZOR IV-PIVOT

BASE PRODUCTS

Dazor products with a 1/2" IV-Pivot can be mounted in a variety of ways.

Note: Most Dazor products can be purchased with a permanent weighted desk base.

IV-Pivot shown at left

If you have a particular mounting situation, please, contact us about various mounting options.

7100-060 WALL MOUNT OR TABLETOP BRACKET

Bracket for vertical mounting to a sturdy, permanent wall. Bracket can also be mounted with screws to a tabletop in a horizontal or sloped position.

7100-075 CLAMP TO HORIZONTAL SURFACE

Rugged plastic dual clamp mounting prevents the base from moving and twisting off the surface.

7100-08 CLAMP TO A SLOPED SURFACE

Adjustable, dual clamp base mounts on sloped surfaces. Clamps onto the right, left, or backside of a tilted table top. Adjustments are made swiftly with the comfortable, easy-to-grasp knob.

7100-093 CLAMP TO HORIZONTAL SURFACE (standard clamp provided with most Dazor lamps)

All metal, dual clamp mounting prevents the base from moving and twisting off the surface.

7100-100 TABLETOP BUSHING MOUNT

Metal bushing for hole drilled in tabletop. Excellent for mounting a Dazor fixture to a work bench

8TR200-6A WALL MOUNT BRACKET

Alternative wall mount for gooseneck arm.

1050 CASTER FLOOR STAND

Heavy-duty 5 casters, Dazor models only., 30 lbs., 40.5"high. Wheels and base black.


3050R PEDESTAL FLOOR STAND

Circular pedestal, Dazor models only, 30 lbs., 38.5" high

7940-04 ADJUSTABLE HEIGHT BRACKET/Floor Stands

Mounts on pole of floor stand and can be adjusted up and down the length of the pole for desired height.

Free-up valuable desktop space by mounting Dazor task lights on workstation wall partitions. Easy-to-install brackets slip into partition slotted channels. Standard 1/2" IV-pivots on Dazor task lights fit into the bracket.





8TR-100

Side View

Front View

8TR-100



Adjustable Bracket

1/2 -inch IV-pivot hole

3/4 inch Panel Depth Adjustment

FRONT VIEW

8TR-100 SINGLE MOUNT Locate the slotted channel closest to the work area you wish to illuminate. Extent of area illuminated is a function of the task light arm reach. One bracket adjusts to most standard and deep wall partitions. Tighten one screw to provide a firm mount for your task light.

Available colors: Black, White, Almond, Dove Gray

Form MT-OP-2.ind



DAZOR®

Dazor Manufacturing Corp.

2079 Congressional Dr. • St. Louis, MO 63146
314.552.2400 • 800.345.9103 • fax 314.542.2069

www.dazor.com • www.specfinder.com • info@dazor.com

